

Han TC70 M-contact 6mm² protected PA



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 7103
Specification	Han TC70 M-contact 6mm ² protected PA
HARTING eCatalogue	https://harting.com/09110007103

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts
Details	Touch protection IPXXB up to a maximum of 1000V AC / 1500V DC

Technical characteristics

Conductor cross-section	6 mm ²
Rated current	≤70 A
Contact resistance	≤0.5 mΩ
Stripping length	15.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy Polyamide (PA)
Surface (contacts)	Silver plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	8.036 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140543034
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522