



USB POWER BANK FACILITY



ADJUSTABLE HEAD FOR LIGHT ANGLE



STRONG MAGNETIC FEET



SAMSUNG
LED CHIP

3000
LUMEN
OUTPUT

3-6
HOURS
RUNTIME

25
METRE
BEAM RANGE

IPX4
WATER
RESISTANCE

SLR-3000 - RECHARGEABLE SITE LIGHT

- 3000 Lumen 30W Samsung® SMD LEDs
- Powerful Li-ion battery with battery level indicator
- Battery pack can easily be removed and used as a USB power bank
- 50% dimming function to increase battery runtime
- Built in aluminium heat sink
- Anti-slip rubber grip handle
- Adjustable head for light angle
- Tough polycarbonate housing and stand
- Acrylic LED diffuser for even light dispersion
- Anti glare polycarbonate lens
- Super strong magnetic base

BATTERY 7.4v 6600 mAh Li-ion Battery Pack
WEIGHT 1880g
DIMENSION 215 x 192 x 285mm



STRONG MAGNETIC FEET



USB POWER BANK FACILITY