

## Features

- Easy unwind and easy to tear
- Good abrasion resistance
- Very high tack
- Clean peel
- Water resistant finish
- Writable surface
- Conformable to awkward shapes
- Non-corrosive abrasive

## RS PRO Duct Tape – 50m x 50 mm

RS Stock No: 146-7414



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

# Duct Tapes

## Product Description

Durable and waterproof, our premium gloss cloth tape exhibits excellent abrasion resistance. Boasting a remarkable combination of very high tack and effortless clean peeling from most surfaces, this tape is user-friendly with easy hand tearing. The tape features a water-resistant finish, making it ideal for outdoor applications. For situations where a clean peel is crucial, we advise conducting a suitability test on the intended surface. Crafted from polycloth with an extruded gloss finish, this tape is equipped with a white, aggressive, pressure-sensitive, and solvent-free rubber resin adhesive.

## General Specifications

Thickness	0.23 mm
Breaking Load	32 N/cm
Elongation	24%
Adhesion to steel	5.5 N/cm
Adhesion to self	3.5 N/cm
RoHS compliant	Yes
Service Temperature	50°C to +80°C
Application Temperature	+10°C to +45°C
Storage Temperature	+12°C to +25°C

## Similar Products

Stock No.	Brand	Product Name
146-7414	RS PRO	RS PRO Duct Tape, 50m x 50mm, Black, Gloss Finish
146-7415	RS PRO	RS PRO Duct Tape, 50m x 50mm, Yellow, Gloss Finish
146-7416	RS PRO	RS PRO Duct Tape, 50m x 50mm, Silver, Gloss Finish
146-7418	RS PRO	RS PRO Duct Tape, 50m x 50mm, Red, Gloss Finish