Optical Fiber Cleaver


OFC35



The NetPeppers OFC35 is the professional device for fiber cleaving. This compact cleaver features a true one-step mechanism that effectively reduces working time.

Time-saving work

True one-step mechanism saves valuable time during the cleave process: simply push down the cover and the cleave process is carried out.



High-quality workmanship

No unintentional folding of the fiber holder and the drop container cover as well as robust and precisely manufactured housing made of aluminum.

Long-term companion

Manufacturing with low tolerances and a high-quality blade with up to 60.000 cutting cycles enables long-term use without annoying maintenance.

Technical Data	Fiber Optic Cleaver OFC35
Supported fiber categories	Singlemode Multimode
Operating principle	One-Step, automatic
Scrap container	Yes, sliding lid, removable
Supported cladding diameter	125 μm
Fiber holder	Four in One (125μm, 250μm, 900μm, 3mm)
Scale	5 - 20 mm
Blade life	$\geq$ 60.000 cleaves
Average cleave angle deviation	$\leq$ 0.5°
Dimensions	73 x 91 x 48 mm (w x d x h)
Weight	219 g
Operating conditions	0 bis 95% humidity and 0 bis 50°C (non-condensing)
Storage conditions	0 bis 95% humidity and -40 bis 80°C (non-condensing)
Scope of delivery	OFC35 Cleaver, transport box, quick start guide, allen key
Order no.	NP-FIBER35



Features

COMPACT DESIGN | RELIABLE CLEAVE PERFORMANCE | LONG SERVICE LIFE | ONE-HANDED OPERATION

NETPEPPERS
FOR BETTER NETWORKS

NetPeppers GmbH ✪ Carl-Benz-Str. 5 ✪ 82266 Inning/Germany
Tel.: +49-89-219097300 ✪ E-Mail: mail@netpeppers.com

© 2025 NetPeppers GmbH. All rights reserved, as well as errors and changes. The NetPeppers logo is a trademark of NetPeppers GmbH.