

Datasheet

Supra W2 Heavy Duty Hose Clamps



Image representative of range

Technical Specifications:

Specifications	
Band & Bridge	X6Cr17 Stainless Steel (DIN 1.4016) (AISI 430)
Bolt	Qst 34-3 Mild Steel (DIN 1.0213) Silver-white Cr3 A Zinc Plated

Features & Benefits:

- **Supra W2 can be mounted in the most awkward applications without having to remove the hose**
- **Can be opened up and fastened again when in place without dislodging any parts of the clamp**

Pressure Rating:

- ***The maximum application pressure can vary depending on the type of hose used and the geometry of the coupling.**

RS Article	Clamping Range	Band Width (mm)	Max Values* Pressure
265-0231	85 - 91 mm	25 mm	25 Bar
265-0247	112 - 121 mm	25 mm	25 Bar
265-0253	162 - 174 mm	28 mm	10 Bar