




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 12

Terminal Block Connector Type: Header

Centerline (Pitch): 3.5 mm [.138 in]

Number of Rows: 1

Operating Voltage: 300 VAC

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	12
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Black
Product Orientation	Right Angle

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
--------------------------------------	----------



Contact Base Material	Copper Alloy
Contact Current Rating (Max)	8 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	3.5 mm[.138 in]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2213936-2
SMT TB SCREW RECEPTACLE, 3.5 MM, 12 POS



TE Part # 2834385-2
RELEASE POKE-IN CONNECTOR_2P_NATURAL




TE Part # 2834334-2
4.0PITCH ITB CONN_2P_W CAP_NATURAL



TE Part # 2834167-3
RELEASABLE SLIM CONTACT

Also in the Series | Buchanan WireMate TB Series



PCB Terminal Blocks(34)

Customers Also Bought




TE Part #8-2176412-1
5W XSM M/OX 5% 11K



TE Part #1-2176088-3
RP 1J 0.166W 1K0 0.1% 25PPM 1K RL



TE Part #7-1625867-3
RP 1J 0.166W 35R7 0.1% 25PPM 1K RL



TE Part #745547-1
HDE 20 KIT,CABLE CLAMP



TE Part #1-2213936-2
SMT TB SCREW RECEPTACLE, 3.5 MM, 12 POS

TE Part #5-146130-4
10 MODII HDR DRST SFMNT B/A LF

TE Part #284506-3
3 POS TERMI-BLOK PLUG STACK 3,

TE Part #2213936-6
SMT TB SCREW RECEPTACLE, 3.5 MM, 6 POS

TE Part #2213936-3
SMT TB SCREW RECEPTACLE, 3.5 MM, 3 POS

TE Part #2213933-6
SMT TB R/A HEADER, RET, 3.5MM, 6 POS

Documents

Product Drawings

SMT TB R/A HEADER, RET, 3.5MM, 12 POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2213933-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2213933-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2213933-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Buchanan WireMate SMT

English

BUCHANAN WireMate Connectors Brochure

BUCHANAN WireMate Connectors Brochure

English