

Hard Polyurethane - TUH

TUH1073BU-100

Datasheet

- Applicable tubing O.D.: Ø 4 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- Colours: black, white, blue and translucent.

Standard specifications

Size	1073 (O.D. Ø10, I.D. Ø7.3)
Color	BU (Blue)
Roll Length	100 m Roll
Pressure medium	Air
Maximum temperature of pressure medium	20 °C
Maximum operating pressure	0.8 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-20 °C
Weight	3.600 Kg

Additional information

Catalogue

[T_EU.pdf](#)