

## PRODUCT PROFILE

### *edding 750 paint marker*



#### **Product text**

- Paint marker for highly opaque and permanent labelling even on dark and transparent materials, e.g. metal, glass and plastic
- The round nib has a stroke width of 2-4 mm
- The paint-like ink is quick-drying, weatherproof, extremely lightfast and wear-resistant
- All colours are heat-resistant up to 400 °C
- The colours yellow, orange, brown, violet, pink, light blue, white and silver remain visible at up to 1000 °C
- The colour white is recommended by Lufthansa Technik
- Available in 14 different colours. The colours brown, violet, pink, light blue and copper are available in a different design with the same ink quality (see edding 750 gloss paint marker)
- Spare nibs are available
- Low-odour ink with no added toluene/xylene
- High-quality aluminium barrel

#### **Target group**

- Professionals in industrial environments e.g. metalworking, engineering, electronic or laboratory who need markers with outstanding attributes for different materials, surfaces and applications
- Users who need to deliver a professional result
- Households with 2+ persons
- Households with organizing, labelling and general marking needs

#### **Benefits for the consumer**

- Long-lasting indoors and outdoors
- Exceptional ink for heat-resistant marks up to 400 °C and some colours are still visible up to 1000 °C
- Visible marking even in compromised lighting conditions
- Foil seal ensures the product is unused when purchased
- Intensive colours
- Broad colour assortment
- High-quality brand product

#### **Product Information**

##### **Product ingredients**

- |                    |                      |
|--------------------|----------------------|
| Solvent based ink  | • Yes                |
| Pigment based ink  | • Yes                |
| Excluded additives | • toluene and xylene |

##### **Product features**

- |                      |                                                  |
|----------------------|--------------------------------------------------|
| Shape of nib         | • round                                          |
| Stroke width         | • 2-4 mm                                         |
| Spare nibs available | • Yes                                            |
| Permanent            | • Yes                                            |
| Low odour            | • Yes                                            |
| Outstanding adhesion | • especially on smooth, porous and dark surfaces |
| Opaque               | • Yes                                            |
| Highly Opaque        | • Yes                                            |
| Waterproof           | • Yes                                            |
| Wear resistant       | • Yes                                            |
| Heat-resistant up to | • 400 °C                                         |

- Weatherproof • Yes
- Smudge-proof • Yes
- Lightfast • Yes
- Extremely lightfast • Yes
- Quick-drying • Yes
- Visible on dark surfaces • Yes
- Applicable on • Paper
- Carton/Cardboard
- Rubber
- Plastic
- Glass
- Wood
- Metal/Steel/Iron
- Concrete/Stone
- Leather
- Porcelain
- Foils
- Cable

**Product material**

- Product material of cap • POM
- Product material of mouthpiece • POM
- Product material of barrel • Aluminium
- Product material of nib • Acrylic

**Colour**

- Colour range of product (number of colours) • 14
- Colour range of product • 001-010, 049, 053-055
- Colour of barrel • 049
- Colour of barrel - name • white
- Communication of writing colour by cap • Yes
- Communication of writing colour by mouthpiece • Yes

	SAP no.	KEA / order no.
Single product	840XXX	4-750XXX
Blister of 1	8282XXX	4-750-1-3XXX
Blister of 2	8281XXX	4-750-2-3XXX

EAN code				
	Single product	Folding box	Outer carton	Shipping carton
001 black	4004764018505	4004764425747	-	4004764069927
002 red	4004764018512	4004764425754	-	4004764069934
003 blue	4004764018529	4004764425761	-	4004764069941
004 green	4004764018536	4004764425778	-	4004764069958
005 yellow	4004764018543	4004764425785	-	4004764069965
006 orange	4004764018550	4004764425792	-	4004764069972
049 white	4004764018642	4004764425884	-	4004764068203
053 gold	4004764498215	4004764498222	-	4004764068210
054 silver	4004764498253	4004764498260	-	4004764068227
Blister of 1 001 black	4004764896202	-	4004764896219	4004764896226
Blister of 1 002 red	4004764859726	-	4004764859733	4004764859740
Blister of 1 005 yellow	4004764859757	-	4004764859764	4004764859771
Blister of 1 049 white	4004764863204	-	4004764863211	4004764863228
Blister of 1 001 black	4004764894581	-	4004764894598	4004764894604
Blister of 1 049 white	4004764894611	-	4004764894628	4004764894635
Blister of 2 049 white (2x 049)	4004764866731	-	4004764866748	4004764866755
Blister of 2 assorted (1x 001, 049)	4004764894253	-	4004764894260	4004764894277
Blister of 1 049 white (TR)	-	-	-	8681221561529
Blister of 1 005 yellow (TR)	-	-	-	8681221561512
Blister of 1 001 black (TR)	-	-	-	8681221561482

---

<b>EAN code</b>				
	Single product	Folding box	Outer carton	Shipping carton
Blister of 1 002 red (TR)	-	-	-	8681221561499

<b>Packaging</b>					
	Net weight	Folding box	Outer carton	Shipping carton	Pallet
Single product	19,4 g	10 pcs	-	400 pcs	16.000 pcs
Blister of 1	19,6 g	-	10 pcs	100 pcs	3.200 pcs
Blister of 2	46,2 g	-	10 pcs	80 pcs	1.920 pcs