

NITREX

Nitrex 290B/290G (290B* | 290G*)

PU palm coated · available in black and grey · 13 gauge seamless liner
breathable · abrasion resistance

Physical Specifications:

Material: Polyester shell
Colour: Black and Grey
Coating: Polyurethane (palm)

Order Codes | Sizing:

290B/06 | 290G/06 | 6
290B/07 | 290G/07 | 7
290B/08 | 290G/08 | 8
290B/09 | 290G/09 | 9
290B/10 | 290G/10 | 10
290B/11 | 290G/11 | 11

Size 06 | XS Size 07 | S Size 08 | M
Size 09 | L Size 10 | XL Size 11 | XXL

Packaging:

10 pairs per polybag
100 pairs per case

Classification:



For more about the Nitrex range, please [click on the image](#)



Features

- Medium weight seamless polyester liner
- Breathable palm coating
- Abrasion resistant
- Polyurethane palm coating

Benefits

- Offers a flexible, close fit and a high level of dexterity and comfort for handling small parts
- Breathable PU gives wearer optimal comfort and allows the hand to breath and prevents perspiration
- To extend the life of the glove and protect the wearer
- Offers excellent dry grip

Sectors

- Construction
- Electricians
- Automotive
- Engineering and Manufacturing
- Warehousing, Transport and Logistics
- General Maintenance



UNIGLOVES UK
Registered in England No: 4010200
VAT registration 791817787

3 Ambley Green, Gillingham Business Park,
Gillingham, ME8 0NJ, UK
+44 (0)800 049 6602
enquiries@unigloves.co.uk
unigloves.co.uk

UNIGLOVES GERMANY
Arzt- & Klinikbedarf
Handelsgesellschaft mbH

Camp-Spich-Straße 71
D-53842 Troisdorf-Spich,
+49 (0) 2241-9323-0
unigloves@unigloves.de
unigloves.de



Neither this document nor any other statement made herein by or on behalf of Unigloves should be interpreted as a guarantee of marketability or that any Unigloves product is fit for a particular purpose. Unigloves accepts no responsibility for the adequacy or suitability of a user's selection of gloves for their intended application.

Issue No. 1

Prepared at Gillingham
on 17/11/21