

4U 19" Fixed Wall Mount Vertical Rack, Patch Panel Bracket Wall Mount for Data/AV/IT/Computer, Vertical Mounting, 4U Rack for Cabinet and Server Room, 180lb (81.6kg) Capacity

Product ID: RK419WALLV2



This 4U 19 in server room rack enables vertical mounting of rack-mounted equipment of any depth. Mount the bracket to a wood stud wall and position equipment vertically, maximizing space utilization and optimizing layout design. The open-frame design allows for unrestricted airflow to the mounted equipment, improving cooling.

Mount the bracket into a wall featuring wood stud construction, where studs are spaced 16in (40.6cm) apart. The patch panel wall mount rack is perfect for SoHo (small office, home office) and other small footprint applications allowing you to vertically mount up to 180lb (81.6kg) of standard rack equipment into this 14-gauge steel bracket. The mounting holes are positioned 16in (40.6cm) apart, matching the standard for construction framework.

The vertical wall mount network rack conveniently includes 6x wood screws, 12x M5 square cage nuts, and 12x M5 screws to attach the rack to a wall and mount your equipment.

The wall mount vertical rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **4U VERTICAL WALL MOUNT RACK:** This patch panel wall mount supports 19" rack-mountable IT/AV/Network

equipment of any depth; 180lb (81.6kg) Weight capacity; EIA-310 and REACH Compliant; Compact wall mount design for minimal footprint in server room/closet

- **READY TO USE:** The wall mount vertical rack ships fully assembled, and includes 6x Wood Screws, and 12x M5 Cage Nuts and Screws for mounting the rack and equipment; Two mounting holes support 16in wood stud spacing
- **BUILT TO LAST:** The vertical rack is constructed with a 14-gauge steel frame; Provides a solid and stable anchor to mount equipment; The powder coated paint and interior corner welding ensures long-lasting use and sturdiness
- **CERTIFIED PACKAGING:** This assembled and ready-to-use communications rack ships with ISTA-6 certified packaging that ensures damage-free delivery; The server room rack is TAA compliant
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this vertical wall mount patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Special Features	Ships Fully Assembled
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	130.0 lb [59.0 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes screws for mounting to wood surfaces, additional hardware will be required for other materials
------	---

Physical Characteristics

Color	Black
Construction Material	Steel



**Product
Measurements**

Product Length	6.1 in [15.5 cm]
Product Width	19.9 in [50.5 cm]
Product Height	7.6 in [19.3 cm]
Weight of Product	0.0 oz [0.0 g]

**Packaging
Information**

Package Length	6.7 in [17.0 cm]
Package Width	20.9 in [53.2 cm]
Package Height	8.5 in [21.6 cm]
Shipping (Package) Weight	4.6 lb [2.1 kg]

What's in the Box

Included in Package	1 - 4U Vertical Wall Mount Bracket
	16 - M5 Screws
	16 - M5 Cage Nuts
	6 - Wood Screws
	1 - Quick-Start Guide

**Product appearance and specifications are subject to change without notice.*