

Coupling
EAMC-42-50-16-16-U
Part number: 8230706

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	16 mm
Mounting diameter 2	16 mm
Size	42
Nominal length	50 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	21 Nm
Product weight	145 g
Note on materials	RoHS compliant