


minimate*



(2.54 mm) .100"

IPS1 SERIES

SHROUDED POWER CONNECTOR SET

SPECIFICATIONS

For complete specifications see www.samtec.com?IPS1

Insulator Material: Black LCP

Contact Material: Phosphor Bronze

Plating:

Sn or Au over 50 µ" (1.27 µm) Ni Operating Temp Range: -55 °C to +105 °C with Tin; -55 °C to +125 °C with Gold Insertion Depth:

(3.81 mm) .150" to (6.48 mm) .255" Wiping Distance:

Wiping Distance:
(0.38 mm) .015"

Voltage Rating:
775 VAC/1095 VDC
Standard Creepage:
(2.55 mm) .100" (without -LC)
(1.08 mm) .043" (with -LC)
Standard Clearance:
(1.75 mm) .069" (without -LC)
(0.62 mm) .024" (with -LC)

RoHS Compliant:

IPT1/IPS1	
PINS	CURRENT RATING (PER CONTACT)
1	5.9 A
2	4.8 A
3	4.1 A
4	3.6 A
50	2.3 A

PROCESSING

Lead-Free Solderable:

Yes SMT Lead Coplanarity: (0.13 mm) .005" max (05-10)* (0.15 mm) .006" max (15-25)* '*(.004" stencil solution may be available; contact IPG@samtec.com)

RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- · Other sizes
- Other platings
- · Latching feature
- · No. 1 position polarized

Some sizes, styles and options are non-standard, non-returnable.



PLATING

OPTION

05, 10, 15, 20, 25 (Standard sizes)

NO. PINS

PER ROW

50

(2.54)

= 10 µ" (0.25 µm) Gold on contact, Matte Tin on tail

Leave blank for Through-hole -VS

OPTION

= Surface Mount

-RA = Right-angle

-LC = Locking Clip (Manual placement

required)


(-VS only)

OTHER

OPTION

–K = (5.50 mm) .217" DIA Polyimide film Pick & Place Pad (-VS only)

> -TR = Tape & Reel Packaging (-VS only)



(4.95)

No. of positions x (2.54) .100 $_{-}$ + (0.38) .015

(2.54)