


UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and flat-ribbon cable connector, for assembly on NS 35/7.5, 10 positions

Commercial data

Item number	2962544
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CK2
Product key	DK21A1
Catalog page	Page 244 (IF-2007)
GTIN	4017918087210
Weight per piece (including packing)	73.5 g
Weight per piece (excluding packing)	68.3 g
Customs tariff number	85369010
Country of origin	DE

UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	10

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 1 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	10
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Number of positions	10
Conductor cross section rigid	0.14 mm² ... 1.5 mm²
Conductor cross-section rigid (2 conductors with same cross section)	0.14 mm² ... 0.75 mm²
Conductor cross section flexible	0.14 mm² ... 1.5 mm²
	0.25 mm² ... 1 mm² (Ferrule without plastic sleeve)
	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross section flexible (2 conductors with same cross section)	0.14 mm² ... 0.75 mm²
	0.25 mm² ... 0.5 mm² (Ferrule without plastic sleeve)
	0.5 mm² ... 1 mm² (TWIN ferrule with plastic sleeve)
Conductor cross section AWG	26 ... 16

UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

Signaling

Status display present	No
------------------------	----

Dimensions

Item dimensions

Width	54 mm
Height	45 mm
Depth	50.42 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>



Drawings

Circuit diagram



UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2962544>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Field wiring	125 V	1 A	-	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Field wiring	125 V	1 A	-	-

cULus Recognized				
-------------------------	--	--	--	--

UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-13.0	27141152
ECLASS-12.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>




Accessories

FLK EZ-DR.../.../... - Cable

2295059

<https://www.phoenixcontact.com/in/products/2295059>

Round cable, with preassembly, not shielded, variable cable length



FLK 10/EZ-DR/ 50/KONFEK - Cable

2299204

<https://www.phoenixcontact.com/in/products/2299204>

Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 0.5 m



UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

FLK 10/EZ-DR/ 100/KONFEK - Cable

2299217

<https://www.phoenixcontact.com/in/products/2299217>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 1 m

FLK 10/EZ-DR/ 150/KONFEK - Cable

2299220

<https://www.phoenixcontact.com/in/products/2299220>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 1.5 m

UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

FLK 10/EZ-DR/ 200/KONFEK - Cable

2299233

<https://www.phoenixcontact.com/in/products/2299233>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 2 m

FLK 10/EZ-DR/ 300/KONFEK - Cable

2299246

<https://www.phoenixcontact.com/in/products/2299246>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 3 m

UM 45-FLK10 - Termination board



2962544

<https://www.phoenixcontact.com/in/products/2962544>

FLK 10/EZ-DR/ 400/KONFEK - Cable

2299259

<https://www.phoenixcontact.com/in/products/2299259>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 4 m

FLK 10/EZ-DR/ 600/KONFEK - Cable

2299262

<https://www.phoenixcontact.com/in/products/2299262>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 6 m

UM 45-FLK10 - Termination board

2962544

<https://www.phoenixcontact.com/in/products/2962544>



FLK 10/EZ-DR/ 800/KONFEK - Cable

2299275

<https://www.phoenixcontact.com/in/products/2299275>



Round cable set; connection 1: IDC/FLK socket strip (1x 10-position); connection 2: IDC/FLK socket strip (1x 10-position); cable length: 8 m

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in