



Type	57937
Designation	USB A to USB C, μUSB or Lightning, Charge & Sync cable
Material	Aluminum, TPE, Nylon
Housing colour :	Black / Titanium
Dimensions:	
Length	200 ± 5cm
Weight	55 ± 3g
Cable diameter	3.5 ± 0.2mm



Max. Voltage :	5V
Max. Current :	2.4A
Max. Wattage :	12W
Max. data transfer rate :	480Mbit/s

Input Voltage/Current:	Min. Output Voltage
5/1A	≥ 4.75V
5V/2A.....	≥ 4.5V

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries