



**Part Number :** [350689902](#)  
**Product Description :** MP-Lock Quick Disconnect,  
Female, for 20x2, 20x18, 18x2 AWG (0.80-0.52mm<sup>2</sup>),  
Metal Strip, Tab 4.75 x 0.51mm, Pre-Tin Plated  
**Series Number :** 35068  
**Status :** Not Recommended For New Design  
**Product Category :** Quick Disconnects




## Documents & Resources

### Specifications

- [PK-35068-001-001.pdf](#)
- [PS-35189-002-001.pdf](#)
- [PS-35189-004-001.pdf](#)
- [PS-35817-001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Not Recommended For New Design
Category	Quick Disconnects
Series	35068
Description	MP-Lock Quick Disconnect, Female, for 20x2, 20x18, 18x2 AWG (0.80-0.52mm <sup>2</sup> ), Metal Strip, Tab 4.75 x 0.51mm, Pre-Tin Plated
Product Name	MP-Lock
Type	Quick Disconnect
UPC	800754375146

### Agency

CSA	LR95446
UL	E92853

### Electrical

Voltage - Maximum	300V
-------------------	------

### Physical

Barrel Type	Open
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.440/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Polarized to Mating Part	Yes
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.50mm max.
Wire Size (AWG)	18, 20

## Mates With / Use With

### Use with Part(s)

Description	Part Number
4.75mm Tab MP-Lock Housings	<u>35189</u>
MP-Lock Receptacle Housings	<u>35817</u>

---

## Application Tooling

### Global

Description	Part Number
Mini-Mac Applicator Rear Feed	<u>638022000</u>