

## **HEATER**

## **RC 016** | 5W

Art. No. 01602.0-05

(Standard version: 01602.0-00)



## TECHNICAL DATA<sup>1</sup>

Heating capacity <sup>2</sup>	5W
Operating voltage	12-24V AC/DC
Inrush current max.	3.5A
Recommended pre-fuse	4.0A
Surface temperature (approx.) <sup>2</sup>	+80°C (+176°F)
Connection	2 x AWG 18 stranded wire, length: 500mm
Operation temperature	-45 to +70°C (-4 to +158°F)
Weight (approx.)	25g
Approvals	-

<sup>&</sup>lt;sup>1</sup> data differs compared to the standard version

<sup>&</sup>lt;sup>2</sup> at +20°C (+68°F) ambient temperature