

'Cig-Arrête® 9—24Vdc Product Versions (Part No CSA-xxx24)



Mode	24Vdc	18Vdc	12Vdc	9Vdc
Start Up Current (mA)	12	16	19	23
Quiescent Current (mA)	0.9	1.0	1.3	1.8
Volume High (mA)	70	90	110	130
Volume Medium (mA)	40	50	60	70
Volume Low (mA)	25	30	40	50
Relay Only (No Voice) (mA)	30	40	50	60
maximum cable distance using 7/0.2 cable	88 ohms per Km	2 core = 176 ohms per Km		
Start Up Current				
max permissible Volt drop	15	9	3	2
100m cable @ 17.6 ohms (Max mA)	850	510	170	112
Max No Of products (High Volume)	12	5	1	0
Max No Of products (Med Volume)	21	10	2	1
Max No Of products (Low Volume)	34	17	4	2

