

## UNI-DICHT-HALB-Verschraubung Pg16



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5058
Specification	UNI-DICHT-HALB-Verschraubung Pg16
HARTING eCatalogue	<a href="https://harting.com/09000005058">https://harting.com/09000005058</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for surface mounted housings

### Technical characteristics

Tightening torque	≤6 Nm (depending on the cable and the seal insert used)
Wrench size	27
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	Pg 16
Clamping range	11.5 ... 15.5 mm

### Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances      Not contained

---

## Commercial data

Packaging size	10
Net weight	6.5 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140001435
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431

---