

Datasheet

## RS Pro G 1/4 Pressure Switch, 250 bar

RS Stock No: **363-6006**



### Product Details

RS Pro pressure switch features 250 bar maximum operating pressure and G 1/4 connection. This pressure switch allows micro switch operation once a pre-set pressure is reached. It can be adjusted via a graduated knob, which can be locked with a grub screw. The pressure switch meets DIN 43650 standards.

### Features and Benefits

- Adjustment is via a graduated knob, which can be locked with a grub screw
- Incorporates a mechanical stop providing over-pressure protection for spring and micro switch
- DIN 43650 connector

**Specifications:**

Connection Thread Size	1/4 in
Connection Thread Standard	G
Connection	G 1/4
Contact Operation	Normally Closed, Normally Open
IP Rating	IP65
LED Indicator	No
Maximum Operating Pressure	250 bar
Maximum Operating Temperature	+80°C
Maximum Pressure Setting	250 bar
Minimum Operating Pressure	30 bar
Minimum Operating Temperature	-20°C
Minimum Pressure Setting	0 bar
Output Range	30 to 250 bar
Output Type	NO/NC
Pressure Setting Range	0 to 250 bar
Pressure Type	Positive Pressure
Type	Adjustable
Voltage Rating	250 V ac/dc
Frequency Rating	120 cpm
Material	Steel
Standards Met	RoHS Compliant