



tesa® 4224

Product Information



Tensilised Strapping Tape

Product Description

tesa® 4224 is a tensilised polypropylene strapping tape with a natural rubber adhesion system and was specially developed for the food and drug industries. tesa® 4224 exhibits good tensile strength and low elongation at the same time. The product has a clean appearance, is highly cold-resistant and, therefore, ideal also for frozen food packaging.

Application Fields

Applications include closure of shipping cartons, palletising, bundling and reinforcing.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Backing material	MOPP	• Total thickness	79 µm
• Type of adhesive	synthetic rubber	• Colour	white

Properties/Performance Values

• Elongation at break	35 %	• No discolouration	yes
• Tensile strength	180 N/cm	• Residue free removal	yes

Adhesion to Values

• steel	6 N/cm
---------	--------

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04224>