

Features

- Specially designed for precision flush cutting in metal.
- Its very fine 1mm tooth pitch combined with a wavy-set design delivers smooth, effortless cuts through thin steel materials.
- Manufactured from durable M2 High Speed Steel, this blade is designed for regular-strength steel and features a standard length of 225mm, providing a cutting capacity of up to 175mm.

Reciprocating Saw Blade - Metal 225 x 19 x 0.9mm - Fine Cut

RS Stock No.: 0757830



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Reciprocating Saw Blade

0757830 Metal Reciprocating Saw Blade is specially designed for precision flush cutting in metal. Its very fine 1mm tooth pitch combined with a wavy-set design delivers smooth, effortless cuts through thin steel materials. Manufactured from durable M2 High Speed Steel, this blade is designed for regular-strength steel and features a standard length of 225mm, providing a cutting capacity of up to 175mm.

- *Manufactured with D6A Shock-Resisting Tool Steel & M2 High Speed Steel Teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Pipes, Profiles and Box Section*
- *Supplied in 5pc Packs*

General Specifications

| | |
|-----------------------|--------------------------------|
| Tooth Design | Side Set, Milled |
| Type | Reciprocating Saw Blade |
| Teeth Spacing | 1.0mm |
| TPI | 24 |
| Thickness | 0.9mm |
| Max Cut Depth | 175mm |
| Cut Type | Fine Cutting |
| Blade Material | M2 High Speed Steel |
| Body Material | D6A Shock-Resisting Tool Steel |
| Fitting | S-Shank 1/2" |
| Length | 225mm |
| Width | 19mm |

| Stock No. | Cut Type | Thickness | Length | Width |
|---------------------|---------------------|-----------|--------|-------|
| XXX-XXXX 0757823 | Progressive Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757824 | Fast Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757825 | Precision Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757826 | Fine Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757827 | Fast Cutting | 0.9mm | 225mm | 19mm |
| XXX-XXXX 0757828 | Precision Cutting | 0.9mm | 225mm | 19mm |
| XXX-XXXX 0757830 | Fine Cutting | 0.9mm | 225mm | 19mm |

Approvals

| | |
|---------------------|-----------|
| Declarations | REACH DoC |
|---------------------|-----------|

Similar Products

| Stock No. | Brand | Product Name | Cut Type | Thickness | Length | Width |
|---------------------|--------|----------------------------|------------------------|-----------|--------|-------|
| XXX-XXXX 0757823 | RS PRO | Reciprocating Saw Blade | Progressive Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757824 | RS PRO | Reciprocating Saw Blade | Fast Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757825 | RS PRO | Reciprocating Saw Blade | Precision Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757826 | RS PRO | Reciprocating Saw Blade | Fine Cutting | 0.9mm | 150mm | 19mm |
| XXX-XXXX 0757827 | RS PRO | Reciprocating Saw Blade | Fast Cutting | 0.9mm | 225mm | 19mm |
| XXX-XXXX 0757828 | RS PRO | Reciprocating Saw Blade | Precision Cutting | 0.9mm | 225mm | 19mm |
| XXX-XXXX 0757830 | RS PRO | Reciprocating Saw Blade | Fine Cutting | 0.9mm | 225mm | 19mm |

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories