

Drawn cup needle roller bearings with open ends HK4016-2RS (Series HK..-2RS)

lip seals on both sides, to DIN 618

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	40 mm	
D	47 mm	
C1	16 mm	Tolerance: 0/-0,3
rmin	0,8 mm	
m	37 g	Mass
Cr	14000 N	Basic dynamic load rating, radial
C0r	24300 N	Basic static load rating, radial
Cur	3250 N	Fatigue limit load, radial
nG Fett	3950 1/min	Limiting speed for grease lubrication
	LR35X40X16,5	Suitable inner ring

IR35X40X17-XL Suitable inner ring

