

Rittal – The System.

Faster – better – everywhere.

► Rail for interior installation AX – AX 2393.350

Date : Apr 23, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Rail for interior installation AX – AX 2393.350

created: 23.04.2020 on www.rittal.com/com-en



Product description

Description:	For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g. for: Punched section with mounting flange 14 x 39 mm, enclosure lights, door-operated switch, door stay, cable conduit holder
Benefits:	Only one screw for attaching the rail inside the enclosure Including adaptor for door-operated switch Compatibility with VX25 accessories Enclosure protection category is retained (no machining required) Automatic potential equalisation May be retro-fitted even with the mounting plate in situ. Suitable for installation via gland plates
Material:	Sheet steel
Surface finish:	Zinc-plated
Assembly instruction:	For installing LED system light, only in conjunction with mounting bracket for interior installation

Product features

To fit:	Enclosure type: AX Depth: = 350 mm
Packs of:	4 pc(s).
Weight/pack:	0.7 kg
Copper weight (kg per piece):	0

EAN: 4028177925298

Customs tariff number: 73269098

ETIM 7.0: EC002625

ETIM 6.0: EC002625

eCl@ss 8.0/8.1: 27189234

eCl@ss 6.0/6.1: 23159101

Product description: AX Rail for interior installation, for D: 350 mm
