

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130109-0026](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Pro-Yellow® Nylon 150W Incandescent Hand Lamp with Side Outlet and Switch, Grips Molded, Cord Type 16/3 SJTW, Cord Length 7.62m (25.0'), Easy Access Metal Guard

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

UL E59049

**General**

Product Family	Portable Lighting
Series	<a href="#">130109</a>
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	<a href="#">Hand Lamps</a>
Product Literature Order No	987650-8053
Product Name	Pro-Yellow®
Type	Hand Lamps
UPC	78678850115
Woodhead	Yes

**Physical**

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Incandescent
Cord Type - Primary	16/3 SJTW
Lamp Type	A21
Lamp Wattage - Maximum	150W
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Old Part Number WT6C-25



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

130109Series