

#### **FEATURES**

- Available in uncoated and polyester coated stainless steel
- Flame retardant
- High tensile strength
- Self-locking design
- Excellent resistance to high temperature, chemicals, weather and abrasion

# RS PRO Black Polyester Coated Stainless Steel Roller Ball Cable Tie, 360mm x 4.6 mm

RS Stock No.: 547-4333



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

These RS PRO stainless steel cable ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. These cable ties have a roller ball design which is self-locking and fast and easy to install. Roller ball ties have a locking ball bearing which grips the tie strap and locks the tie as it is tensioned

#### **General Specifications**

| Туре                          | Roller Ball   |  |  |
|-------------------------------|---|--|--|
| Colour                        | Black   |  |  |
| Material                      | Polyester Coated Stainless Steel  |  |  |
| Application                   | Bundling wire together applications in industries such as Oil and gas, Marine, Chemical |  |  |
| Resistant To                  | Resistance to high temperature, chemicals, weather and abrasion                         |  |  |
| Minimum Operating Temperature | -80°C   |  |  |
| Maximum Operating Temperature | 150°C   |  |  |
| Fire Behaviour                | Self-Extinguishing  |  |  |
| Quantity                      | 100   |  |  |

#### **Mechanical Specifications**

| Length                  | 360mm  |
|-------------------------|--------|
| Width                   | 4.6mm  |
| Tensile Strength        | 436.1N |
| Maximum Bundle Diameter | 100mm  |

### **Approvals**

| Standards Met | IEC 62275 (2006), UL-1565 |
|---------------|---------------------------|
|               |                           |





## Non-Releasable Stainless Steel Cable Tie

| RS Part No. | Length mm | Width mm | Max Bundle Dia |
|-------------|-----------|----------|----------------|
| 1595329     | 360       | 4.6      | 100            |
| 1595313     | 200       | 7.9      | 50             |
| 1595357     | 150       | 4.6      | 50             |
| 1595335     | 360       | 7.9      | 100            |
| 5474305     | 520       | 4.6      | 150            |
| 5474311     | 520       | 7.9      | 150            |
| 7436162     | 680       | 4.6      | 200            |
| 7436166     | 380       | 7.9      | 200            |
| 7436172     | 1000      | 4.6      | 300            |
| 7436178     | 840       | 7.9      | 250            |
| 7436181     | 1000      | 7.9      | 300            |

## **Coated Stainless Steel Cable Tie**

| RS Part No | Length mm | Width mm | Max Bundle Dia |
|------------|-----------|----------|----------------|
| 5474327    | 150       | 4.6      | 50             |
| 5474333    | 360       | 4.6      | 100            |
| 5474349    | 250       | 4.6      | 150            |
| 5474355    | 200       | 7.9      | 50             |
| 5474377    | 360       | 7.9      | 100            |
| 5474383    | 520       | 7.9      | 150            |