

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for solid contacts from the CK4.0 ED... series, two marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Your advantages

- Marked die stations for precise processing of corresponding cross sections
- Rotating positioning aid ensures precise contact positioning in the crimping area

Commercial data

Item number	1314533
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BH3135
GTIN	4063151571146
Weight per piece (including packing)	738.6 g
Weight per piece (excluding packing)	738.6 g
Country of origin	SE

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Technical data

Notes

Note on application	For 6.0 mm ² ... 10.0 mm ² turned crimp contacts from the CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	---

Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Marked die stations
	Including positioning guide

Crimping position 1

Max. cross section	6 mm ²
AWG max	10

Crimping position 2

Max. cross section	10 mm ²
AWG max	8

Connection data

Conductor connection

Cross section range, metric	6 mm ² ... 10 mm ²
Cross section range AWG	10 ... 8

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black (RAL 9005)
Material	Steel

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1314533>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Classifications

ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

Accessories

CRIMPFOX-TC HC 10/DIE - Replacement die

1324135

<https://www.phoenixcontact.com/in/products/1324135>



Replacement die for CRIMPFOX-TC HC 10, CK 4,0-ED... turned contacts,
2 marked die stations

CRIMPFOX/ SPR-1 - Replacement spring

1212069

<https://www.phoenixcontact.com/in/products/1212069>



Spare recuperating spring

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

CK4,0-ED-10,00M AG - Crimp contact

1274091

<https://www.phoenixcontact.com/in/products/1274091>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 10 mm² ... 10 mm², AWG 8

CK4,0-ED-10,00F AG - Crimp contact

1274085

<https://www.phoenixcontact.com/in/products/1274085>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 10 mm² ... 10 mm², AWG 8

CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/in/products/1314533>

CK4,0-ED-6,00M AG - Crimp contact

1274092

<https://www.phoenixcontact.com/in/products/1274092>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 6 mm² .. 6 mm², AWG 10

CK4,0-ED-6,00F AG - Crimp contact

1274086

<https://www.phoenixcontact.com/in/products/1274086>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 6 mm² .. 6 mm², AWG 10

CRIMPFOX-TC HC 10 - Crimping pliers

1314533

<https://www.phoenixcontact.com/in/products/1314533>



UNIFOX RT-CK 4.0 - Contact removal tool

1072064

<https://www.phoenixcontact.com/in/products/1072064>

Contact removal tool, for rotated CK-4,0-... contacts



CRIMPFOX/ SPR-1 - Replacement spring

1212069

<https://www.phoenixcontact.com/in/products/1212069>

Spare recuperating spring



CRIMPFOX-TC HC 10 - Crimping pliers

1314533

<https://www.phoenixcontact.com/in/products/1314533>



CRIMPFOX-TC HC 10/DIE - Replacement die

1324135

<https://www.phoenixcontact.com/in/products/1324135>



Replacement die for CRIMPFOX-TC HC 10, CK 4,0-ED... turned contacts,
2 marked die stations

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in