

Day/night mini outdoor camera

Art. no. TVCC40010

Page 1 of 1

- Compact day/night vision mini outdoor camera
- Varied camera installation options - whether indoors or outdoors
- Simple design and high protection class (IP66)
- High detailed resolution, thanks to 600 TVL
- 1 x 20 metre coaxial cable included
- Ideal for extension of TVVR30004 or TVVR30104

Unobtrusive monitoring indoors or outdoors

The analogue day/night mini outdoor camera is the ideal supplement to the TWR30004 4-channel recorder and the TVVR30104 video surveillance kit. It stands out with its plain, unobtrusive design and high protection class (IP66), which means it can be used both outdoors and indoors without an additional weatherproof housing. With a high, detailed resolution of 600 TVL, it delivers precise video images for accurate recognition of persons.

Flexible mounting options

Fast and easy installation is guaranteed with the 20 m combination cable and power supply unit provided.

Technical Data:

Dimensions	150 x 70 mm
Connections	Video signal (BNC), power supply (DC)
Image sensor	1/3" DIS
Pixels (effective)	720 (H) x 480 (V) pixel
Aperture at minimum illumination (color)	0,1 Lux
Aperture at minimum illumination (IR)	0 Lux
Electronic shutter	1/25 ~ 1/15.000 sek.
Backlight compensation	Yes
Height	150 mm
Horizontal angle of view	68,4 °
IR LEDs	12
IR range	10 m
Camera type	Day/night outdoor camera
Max. operating temperature	+ 50 °C

Max. humidity	max. 90 %
Min. operating temperature	- 20 °C
Net weight	0.36 kg
Lens	3.6 mm, fixed lens mm
Noise reduction	> 52 dB
IP protection class	66
DC voltage supply	12 V
Power consumption	max. 420 mA
Day/night switching	Electromechanical IR-cut filter
TVL	600 TVL
Video system	PAL / NTSC