

## FEROX PRIMER - METAL FILLER PRIMER

### DESCRIPTION

Ferox Primer - Metal Filler Primer is a quick-drying acrylic primer designed to fill and smooth surfaces with small scratches and imperfections. It is suitable for any metal surface and bodywork. Before overpainting, sand lightly with very fine grit sandpaper if necessary. The spray button is designed to reduce drips and ensure uniform spray patterns. Suitable for both interior and exterior use.

### APPLICATION

- Suitable for: General metal surfaces

### CLASSIFICATION

Directive 2004/42/EC: VOC  
Subcategory E: Special Finishes  
VOC Limit Value: 840 g/L  
Actual Max Content: 616 g/L

### USAGE

#### Surface Preparation:

Clean the surface thoroughly by removing loosely adhering rust, dust, grease, and oil. Preferably use a solvent such as white spirit or acetone.

#### Application:

Shake the can vigorously for at least two minutes. Spray from a distance of 20-30 cm. For best results, apply 2-3 light, crisscross coats at intervals of 3-5 minutes. After use, invert the can and spray until only gas is released to clean the nozzle. Apply a topcoat 24-48 hours after application. Any product stains can be removed with acetone and/or nitro thinner.

### WARNINGS

Do not use on surfaces previously treated with synthetic paints.

### STORAGE

At least 3 years if stored under the following conditions: in the original sealed container, away from direct sunlight, at temperatures between 5°C and 35°C.

### PACKAGING

Code 2101 Aerosol can of 400 ml

---

## CHARACTERISTICS

- **Appearance:** Aerosol
- **Color:** White
- **Odor:** Solvent
- **Composition:** Acrylic resins
- **Dry Film (2/4 coats):** 12/35 microns
- **Coverage:** 1.5 - 2 m<sup>2</sup>
- **Dust-Free:** 10 minutes
- **Touch Dry:** 20 minutes
- **Fully Dry:** 24 hours
- **Temperature Resistance:** 100-120°C

### NOTES

For safety information about the product, please refer to the safety data sheet.