

Data sheet

Commercial Art.No.: 92.050.6953.1

Distributor GST18i5V 3P1 B V SW

GST18i5 H-distributor, 5 pole, 1 IN, 3 OUT, with mounting option on separate mounting plate, coding mains 250/400 V, 20 A, coding color black



Commercial Art.No.	92.050.6953.1
EAN	4049088350863
Order Unit	20

Certificates / Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V / 400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Lockable	self-locking (unlocking by tool)
Color of coding/ contact carrier	black
Marking of poles	3, N, PE, 2, 1

Model

Number of inputs	1
Number of outputs	3
Type of fastening	Yes
Degree of protection (IP)	IP20
Type of distributor	H-distributor

Material

Housing material	Polyamide
halogen free	Yes
Contact material	CuZn
Fire load	0 kWh
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	59 mm
--------	-------

Width	57.4 mm
Height	40 mm

Classification

ECLASS 8.1	27440603
ETIM 7.0	EC002567
ETIM 6.0	EC002567
ETIM 5.0	EC002567
ETIM 4.0	EC002567