



Main

Range	Resi9
Product or component type	Control block
Accessory / separate part category	Installation accessory
Quantity per set	1

Complementary

Range compatibility	Opale Resi9
[In] rated current	90 A
Enclosure mounting	Wall mounted
9 mm pitches	36
Total number of 18 mm modules	18
Net weight	2.35 kg
Width	357 mm
Height	250 mm
Depth	135 mm
Colour	White (RAL 9003)

Environment

Product certifications	ERDF CPT M&S SPE 13006A
Electrical insulation class	Class II
Fire resistance	750 °C conforming to IEC 60695-2-11
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Ambient air temperature for operation	-15...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations