

PRODUCT-DETAILS

TC5102-NDT

MTG BASE .75X.5IN DETEC NYLON SCREW



General Information

Extended Product Type	TC5102-NDT
Product ID	7TAG009660R0015
EAN	5415022188233
Catalog Description	MTG BASE .75X.5IN DETEC NYLON SCREW
Long Description	Low-Profile Detectable Mounting Base, Detectable Blue Nylon 6.6, Length of 19.1mm (0.75 Inches), Width of 12.7mm (0.50 Inches), Height of 3.05mm (0.12 Inches), Screw Mounting Method, #8 Screw, 100 Pack

Ordering

EAN	5415022188233
UPC	786209015402

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	4 in 102 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	8 in 203 mm
Package Level 2 Units	500 piece
Package Level 2 Width	9.25 in 235 mm

Package Level 2 Height	5 in 127 mm
Package Level 2 Depth / Length	9 in 229 mm

Additional Information

Brand / Label	Ty-Rap
Color	Blue
Effective Date	20121009
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Mounting Base
Special Functions	Detectable with metal and X-ray detection equipment.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5102-NDT
Instructions and Manuals	TC5102-NDT
REACH Declaration	9AKK107992A3997
RoHS Information	9AKK107991A8364

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

