

Datasheet

Stock No: 219-263

RS Pro C 16-1 Series, Female Crimp Circular Connector Contact



Product Details

RS Heavy Duty Connector Kits

RS heavy duty connector kits are a practical solution for industrial applications

Zinc die cast alloy

Powder coating finish

Steel / zinc coated locking lever

Mechanical life: + 500 cycles

Temperature range: - 40°C to +100°C

Protection rating: IP65

Lever locking system

Conforms to DIN 43652

Contacts are ordered separately



ENGLISH

Specifications:

Gender	Female
Wire Size	16 → 14 AWG
Termination Method	Crimp
Series	C 16-1
Contact Plating	Silver
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+100°C