

Sleeve frame - VC-TR2/3M-PEA - 1607062

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve frame, with PE connection to housing, for contact insert modules, type 2, number of insert modules: 3

The illustration shows the version VC-TR 1/2 M-PEA

Why buy this product

- Compact design
- Universal connection
- Proven COMBICON technology
- Can be keyed to prevent incorrect connection



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 940898
Weight per Piece (excluding packing)	15.98 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	27.5 mm
Width	65.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Type	VC2
Color	black
Material	PA-GF

Sleeve frame - VC-TR2/3M-PEA - 1607062

Technical data

General

Housing material	Plastic
Inflammability class according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189239
eCl@ss 6.0	27144001
eCl@ss 7.0	27144001

ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000007
ETIM 5.0	EC000007

UNSPSC

UNSPSC 6.01	43172601
UNSPSC 7.0901	31261501
UNSPSC 11	43172601
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

Sleeve frame - VC-TR2/3M-PEA - 1607062

Approvals

EAC

Drawings

