


regulator plate

VABF-S4-1-R6C2-C-6

Part number: 546247

FESTO

For valve terminals VTSA and VTSA-F, standard port pattern to 15407-2, up to max. 6 bar.



Data sheet

Feature	Value
Width	26 mm
Based on the standard	ISO 15407-2
Assembly position	Any
Controller function	Output pressure constant with secondary exhaust
Pressure gauge selection	possible
Pressure regulation range	0.5 ... 6 bar
Inlet pressure 1	0.5 ... 10 bar
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP65 NEMA 4
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-5 ... 50 °C
Product weight	448 g
Pressure gauge connection	with retaining clamp
Material control panel	PA
Material regulator housing	Aluminium die cast