

1651DGTB

Digital vernier, reading to 0.01 mm

CE

UNI EN ISO 13385-1DIN

Features:

- Reading to 0.01 mm
- Screw slider locking
- Mm/inch conversion
- Zero setting at any position
- Square depth rod up to 300 mm
- In hard plastic case

art.	art.	A Max mm	L mm	B mm	G mm	HxS mm
016510211	1651DGTB 150	150	235	40	0,01-0,0005	16x3
016510212	1651DGTB 200	200	285	50	0,01-0,0005	16x3
016510213	1651DGTB 300	300	400	60	0,01-0,0005	16x3

