

# Line Trimmer XGT®

## UR017G

40Vmax, 330 mm, 600 W

**Model UR017G is a Linetrimmer powered by 40Vmax XGT® Li-Ion battery**

This brushless model is a cordless solution for 23cc class entry-level engine Line trimmers. The main features and benefits are: Lightweight design, Good tool weight balance, Loop handle, Automatic torque drive technology (ADT), Active feedback sensing technology (AFT).



**XGT** **BL** **ADT** **AFT**  
MOTOR

### Technical specifications

|                                            |                                      |
|--------------------------------------------|--------------------------------------|
| Voltage XGT                                | ✓                                    |
| Nominal Battery Voltage                    | 40 V                                 |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion                               |
| No load speed                              | 3500 / 5300 / 6500 min <sup>-1</sup> |
| Cutting width                              | 230 / 255 / 330 mm                   |
| Spindle Thread                             | M10 x 1,25 LH                        |
| Handle Type                                | L                                    |
| Sound Power Level (L <sub>WA</sub> )       | 94,1 dB(A)                           |
| Sound Pressure Level (L <sub>pA</sub> )    | 82,2 dB(A)                           |
| Noise Uncertainty (K Factor)               | 1,5 - 3 dB(A)                        |
| Product net weight                         | 3,5 kg                               |
| Tool weight with battery                   | 4,2 - 4,8 kg                         |
| Product Dimensions (L x W x H):            | 1792 x 362 x 265 mm                  |
| Nylon line- Diameter                       | 2,0 mm                               |

### User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Reverse switch for easy removal of grass clippings from the cutting tool
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Well-balanced and lightweight for superior handling and performance

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

## Other

User manual

Parts drawing