



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put thermoplastic (1 track)
Type of approach	Lateral approach

Complementary

Switch actuation	By specific cam
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature
Ambient air temperature for storage	-40...70 °C standard environment -40...70 °C low temperature
Environmental characteristic	Low temperature Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------