



Main

Range	Actassi
Product or component type	Singlemode fibre optic adapter
Provided equipment	Without screws
Colour	Blue
Type of packing	Bag
Quantity per set	1

Complementary

Minimum number of matings	500 cycles
Optic fiber diameter	9/125 µm
Fibre performance	OS1 OS2
Connector type	SC duplex
Material	Zirconia: ferrule
Fixing mode	By clips Screws
Width	34.8 mm
Height	9.4 mm
Length	27.6 mm
Targeted region	Asia Pacific. Europe

Environment

Ambient air temperature for operation	-25...85 °C
Ambient air temperature for storage	-25...85 °C
Standards	SC adapter: TIA/EIA-604-3 SC adapter: IEC 61754-4 Ed.2 ISO/IEC 11801:2011 Ed.2.2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations