

29598

Aluminium Handle, Ø25 mm,
1460 mm, Purple



This handle with colour-coded grip can be used with any product in the Vikan range.

Technical Data

Item Number	29598
Material	Anodised Aluminium Polypropylene
Complies with (EC) 1935/2004 on food contact materials¹	Yes
FDA compliant raw material (CFR 21)	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	900 Pcs.
Quantity Per Layer (Pallet)	1 Pcs.
Box Length	1480 mm
Box Width	160 mm
Box Height	60 mm
Product Diameter	25 mm
Length/Depth	1460 mm
Width	25 mm
Height	25 mm
Gross Weight	0,35 kg
Net Weight	0,33 kg
Cubik metre	0,0009 M3
Recommended sterilisation temperature (Autoclave)	100 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	8 pH
Recycling Symbol "7", Miscellaneous Plastics	No
GTIN-13 Number	5705020295980
GTIN-14 Number (Box quantity)	15705020295987
Commodity Code	76082020
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.