

Mounting plate 3NP1123 (NH000 up to 160 A), 3NP1133 (NH00 up to 160 A), H:
250 mm W: 800 mm



Model	
product brand name	SIVACON S4
General technical data	
surface processing	Galvanized
product feature perforated	Yes
Mechanical Design	
height	250 mm
width	800 mm
depth	400 mm
net weight	2.65 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

other	Environment
Miscellaneous	Environmental Con- firmations
	Environmental Con- firmations

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
 Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
 Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ6000-3BA82>
 Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/8PQ6000-3BA82>
 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ6000-3BA82
 CAx-Online-Generator
<http://www.siemens.com/cax>
 Tender specifications
<http://www.siemens.com/specifications>

