










## Crimping dies:

Dies	 mm <sup>2</sup>	Terminals series	Dies 	Adapters
	10	preinsulated ELP series	ELP460	U137-460
	16	preinsulated FLP series	FLP460	U137-460
	25	preinsulated NP series	NP460	U137-160
	10	non insulated ELS series	ELS460 or C12 ELS	U137-460 or U137C12
	16	non insulated FLS series	FLS460 or C12 FLS	U137-460 or U137C12
	25	non insulated TN 25 series	C12TN25	U137C12
	35	non insulated TN35 series	C12TN35	U137C12
	50	non insulated TN 50 series	C12TN50	U137C12
	70	non insulated TN70 series	C12TN70	U137C12
	95	non insulated TN95 series	C12TN95	U137C12
	120	non insulated TN120 series	C12TN120	U137C12
	150	non insulated TN150 series	C12TN150	U137C12
	185	non insulated TN185 series	C12TN185	U137C12
	240	non insulated TN240 series	C12TN240	U137C12

 Cross section  
(mm<sup>2</sup>)

Unless otherwise stated,  
all dimensions are in millimeters