

## ICC20\_H\_BS\_ST\_CG\_13-17\_EMC



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 1515
Specification	ICC20_H_BS_ST_CG_13-17_EMC
HARTING eCatalogue	<a href="https://harting.com/97000001515">https://harting.com/97000001515</a>

### Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight EMC version

### Version

Size	20
------	----

### Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	13 ... 17 mm

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE
Colour (seal)	Blue



**Pushing Performance**  
Since 1945

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

## Commercial data

Packaging size	1
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405