

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Ensures easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards.

RS PRO 16.02 mm Flanged Plain Bearing

RS Stock No: 529-041



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance and durability. Made from sintered bronze, it offers excellent wear resistance and is ideal for use in various industrial settings. The bearing's flanged design ensures easy installation and secure positioning.

General Specifications

Bore Size	16.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	20.05 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------