

Eaton 191099

Catalog Number: 191099

Eaton Moeller® series MSF Adapter, 16 A, Pole 3, For use with MSC-DS7, 16 A



General specifications

Product Name	Catalog Number
Eaton Moeller® series MSF Accessory Adapter	191099
	EAN
	4015081915972
Product Length/Depth	Product Height
240 mm	65 mm
Product Width	Product Weight
45 mm	0.188 kg
Certifications	
UL 508	

Product specifications

Special features

Terminal capacity: 2.5 mm² (AWG 14)

Type

Busbar adapter

Adapter width

45 mm

Busbar distance

60 mm

Busbar thickness - max

2 mm

Busbar thickness - min

2 mm

Nominal current

16 A

Number of DIN rails

1

Rail width

24 mm

Voltage rating at AC

690 V

Number of poles

Three-pole

Electric connection type

3 conductors AWG 12

Mounting rail armament

1 mounting rail

Rated operation current (I_e)

16 A

Resources

Brochures

[eaton-msfs-motor-starter-feeder-system-brochure-br034005en-en-us.pdf](#)

Catalogs

[Product Range Catalog Switching and protecting motors](#)

[Switching and protecting motors - catalog](#)

Declarations of conformity

[DA-DC-00004638.pdf](#)

[DA-DC-00004626.pdf](#)

Drawings

[eaton-manual-motor-starters-msf-adapter-dimensions-007.eps](#)

[eaton-manual-motor-starters-msf-adapter-3d-drawing-005.eps](#)

eCAD model

[ETN.191099.edz](#)

Installation instructions

[IL015082ZU.pdf](#)

Installation videos

[Motorstarter Feeder System MSFS](#)

mCAD model

[DA-CS-adapter_msfa1_16](#)

[DA-CD-adapter_msfa1_16](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia