

A43.20.063 0 °C ... 60 °C L1=100 x 9 mm alu CL.2

Bimetallic thermometer, for heating technology A43

Item number: 14138740
Quantity: 1 pcs.
Order code: A4320063H-C1C-100ECKBB-1ZZZZZ1-KSS2ZZZ
Overview: A43.20.063 0 °C ... 60 °C L1=100 x 9 mm alu CL.2
Case material: steel, zinc plated
pointer: plastic, black
Window: polystyrene, PS
Thermowell: detachable, friction retained; Brass
Process connection [E, d6]: G1/2B
WIKA
Dial color, 1-colored

Details: Bimetallic thermometer, for heating technology A43
Model: A43
Design: standard, steel case
Nominal size [NG, d1]: 63 mm
Case material: steel, zinc plated
Unit: °C
Scale range: 0 °C ... 60 °C
Insertion length [L1]: 100 mm
Stem diameter [d5]: 9 mm
Stem material: aluminum
Thermowell: detachable, friction retained;
Thermowell material: Brass
Process connection [E, d6]: G1/2B
Manufacturer logo: *WIKA*
Dial printed (Number of colors): Dial color, 1-colored
pointer model: plastic, black
Window: polystyrene, PS
Accuracy class: class 2 per EN 13190