

Datasheet

RS Pro 17mm Plain Stainless Steel Aerotight Locking Nut, M10, 316, A4

RS Stock No: **665-5619**



Product Details

RS Pro self locking aero tight stiff nut has a type-316, A4 grade stainless steel construction for corrosion resistance. The nut is designed to stay in position despite conditions of severe vibration. This 17 mm locking nut features M10 metric threads to stays in position, whether tightened or not. The nut is suitable for use in highly corrosive environments.

Features and Benefits

- All metal construction
- Suitable for use up to 300°C
- Stays in position whether tightened or not
- Suitable for use in highly corrosive environments
- Reusable



Specifications:

Finish	Plain
Material	Stainless Steel
Stainless Steel Type	316, A4
Thread Size	M10
Type	Aerotight
Thickness	12.03 mm
Thread Pitch	1.5
Width Across Flats	17 mm
Wrenching Height	7.62 mm