

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Angle Drill

PRO GRD 18V-127 HX



Powerful performance with best tool control

The most important data

Torque (soft/hard/max.)	70/100/- Nm
No-load speed (1st gear / 2nd gear)	0 – 550 / 0 – 1,800 rpm
Battery voltage	18.0 V

Part Number 0 601 9N5 100

Technical data

Technical data

Torque (soft/hard/max.)	70/100/- Nm
No-load speed (1st gear / 2nd gear)	0 – 550 / 0 – 1,800 rpm
Battery type	Lithium-Ion
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	215 x 481 x 107 mm
Chuck type	Bit holder with hexagonal shank
Belt clip option	+
KickBack Control	+
Drilling diameter in wood auger bit max	38 mm / 32 mm
Drilling diameter in wood hole saw max	127 mm / 102 mm
Work light	+
Corner distance	43 mm
Drilling diameter in steel twist drill bit max	13 mm / 8 mm
Belt hook type	Hanging hook
Tool fitting/shank	7/16 quick change chuck
Drill dia. in wood hole saw with self feed bit max	65 mm / 51 mm

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Best tool control: Advanced KickBack Control reduces the risk of rotational torque reaction
- Easy handling: Fast and easy accessory change thanks to Quick Change System
- Strong performance: Powerful brushless motor and 2 speed settings for fast, efficient drilling

**HEAVY
DUTY****0-550/
1800**
min⁻¹/rpm**AMP-Share**
BOSCH**PROFESSIONAL
18V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

