

Pneum. contact metal ID 6 female

		Part number	09 14 000 6406	
		Specification	Pneum. contact metal ID 6 female	
		HARTING eCatalogue	https://b2b.harting.com/09140006406	
Identification				
Category	Contacts			
Type of contact	Pneumatic co	ontact		
Description of the contact	Without shut- Straight	off		
Version				
Gender	Female			
Technical characteristics				
Limiting temperature	-20 +85 °C			
Operating pressure	≤10 bar			
Tube inner diameter	6 mm			
Material properties				
Material (contacts)	Brass			
Material (seal)	NBR			
RoHS	compliant with	h exemption		
RoHS exemptions	6(c): Copper	6(c): Copper alloy containing up to 4 % lead by weight		
ELV status	compliant with	compliant with exemption		
China RoHS	50			
REACH Annex XVII substances	No			
REACH ANNEX XIV substances	No	No		
REACH SVHC substances	Yes			

Page 1 / 2 | Creation date 2019-11-14 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties	
REACH SVHC substances	Lead
Specifications and approvals	
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Commercial data	
Packaging size	10
Net weight	11 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors