

FEATURES

- **Graphite material:** Provides excellent thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650°C:** Ensures performance in extreme heat conditions
- **Rotary speed of 30 m/s:** Capable of handling high-speed rotary applications
- **14mm section:** Offers robust sealing capability

RS PRO 8m Graphite Gland Packing, 14mm Section

RS Stock No: 606-567



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a high-performance gland packing solution designed for demanding industrial applications. This graphite gland packing is ideal for sealing in high-pressure and high-temperature environments, ensuring reliable performance and longevity.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	14 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------