




Datasheet IEC Bolt Thermocouple with 2m of Glass Fibre Stainless Steel Over Braided Cable

Available in type 'K' or 'J'



Bolt sensors is generally screwed into the surface which normally increases the speed of response and sensitivity of the measurement. Suitable for use up to +250°C.

- Available in type 'K' or 'J'
- Bolts have grounded junctions
- Bolt thread/pitch sizes available:

M8 x 1mm M10 x 1mm M12 x 1mm

- Bolt lengths available 13 or 25mm
- Each bolt has 2 metres of glass fibre stainless steel over braided cable, terminating in bare tails
- Suitable for use up to +250°C

Туре	Thread Pitch	Thread Length	Cable Length	RS Order Code
J	M8 x 1mm	13mm	2m	872-2569
J	M8 x 1mm	25mm	2m	872-2578
J	M10 x 1mm	13mm	2m	872-2571
J	M10 x 1mm	25mm	2m	872-2575
J	M12 x 1mm	13mm	2m	872-2584
J	M12 x 1mm	25mm	2m	872-2587
к	M8 x 1mm	13mm	2m	872-2581
К	M8 x 1mm	25mm	2m	872-2590
К	M10 x 1mm	13mm	2m	872-2593
К	M10 x 1mm	25mm	2m	872-2597
К	M12 x 1mm	13mm	2m	872-2607
К	M12 x 1mm	25mm	2m	872-2600